

Argo® Headlamp

Case Material: Yellow ABS Case

Dimensions: Height: 2.15 in. (5.46 cm)
Maximum Width: 2.9 in. (7.37 cm); Maximum Depth: 2.25 in. (5.72 cm)

Weight: 4.75 oz with batteries and strap (134.66 grams)

Lens: Unbreakable polycarbonate lens.

Light Source: One C4 LED - 2.5X brighter than a super high flux LED

Light Output: Three (3) digitally controlled brightness levels:
High: Up to 1,300 candela (peak beam intensity); 56 lumens
Medium: Up to 575 candela (peak beam intensity); 25 lumens
Low: Up to 250 candela (peak beam intensity); 11 lumens

On/Off: Pushbutton – hold three (3) seconds for “blink mode”

Run Time: High: 7 hours continuous runtime
Medium: 12 hours continuous runtime
Low: 20 hours continuous runtime

Battery: Three (3) “AAA” alkaline batteries.


- Features:
- LED battery indicator
 - Rubber hard hat strap and elastic strap
 - 90 degree tilting head
 - Water-resistant design

Approvals: Most models meet applicable European Community Directives

Warranty: Limited lifetime warranty



**With batteries (included in purchase).
Made in China*



Item	UPC	Part #
Argo Yellow	080926-61301-0	61301



STREAMLIGHT

30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax • www.streamlight.com