

The HL® Series has gone hands free! When your task requires both hands and a bright light with a wide, flood beam, reach for the ProTac HL Headlamp. It produces 635 lumens of light that reaches 184 meters.



Rubber strap firmly stays in place on helmets and hard hats




- Adjustable elastic strap fits comfortably
- 90° tilting head reduces neck fatigue



TEN-TAP® Programmable switch

**635
LUMENS!**



Maximum illumination beam

TEN-TAP® Programmable switch allows user selection of one of three different programs: 1.) High/medium/low (default); 2.) High only; 3.) Low/medium/high

Three lighting modes:

- High for super-bright light with far-reaching beam distance: 635 lumens; 8,500 candela; 184m beam; runs 1.75 hours
- Medium for bright light and longer run time: 105 lumens; 1,450 candela; 76m beam; runs 8 hours
- Low for extended run time when a less intense beam is ideal: 20 lumens; 280 candela; 33m beam; runs 36 hours

Solid State power regulation provides maximum light output throughout battery life

Uses two 3V CR123A lithium batteries (included)

Durable, anodized aluminum construction
Gasket-sealed, glass lens
IPX4 water-resistant; 1 meter impact resistance tested

6.6 oz (187 grams) with batteries

Limited Lifetime Warranty
Visit www.streamlight.com for full warranty information

#61304 - ProTac HL Headlamp with elastic and rubber straps

The HL[®] Series has gone hands free! When your task requires both hands and a bright light with a wide, flood beam, reach for the ProTac HL Headlamp. It produces 635 lumens of light that reaches 184 meters.



Rubber strap firmly stays in place on helmets and hard hats




- Adjustable elastic strap fits comfortably
- 90° tilting head reduces neck fatigue



TEN-TAP[®] Programmable switch

**635
LUMENS!**



Maximum illumination beam

TEN-TAP[®] Programmable switch allows user selection of one of three different programs: 1.) High/medium/low (default); 2.) High only; 3.) Low/medium/high

Three lighting modes:

- High for super-bright light with far-reaching beam distance: 635 lumens; 8,500 candela; 184m beam; runs 1.75 hours
- Medium for bright light and longer run time: 105 lumens; 1,450 candela; 76m beam; runs 8 hours
- Low for extended run time when a less intense beam is ideal: 20 lumens; 280 candela; 33m beam; runs 36 hours

Solid State power regulation provides maximum light output throughout battery life

Uses two 3V CR123A lithium batteries (included)

Durable, anodized aluminum construction
Gasket-sealed, glass lens
IPX4 water-resistant; 1 meter impact resistance tested

6.6 oz (187 grams) with batteries

Limited Lifetime Warranty
Visit www.streamlight.com for full warranty information

#61304 - ProTac HL Headlamp with elastic and rubber straps