



SEE WHY TIGHTSIGHT® IS YOUR ONLY CHOICE.

The new **TightSight® Clamp Meters** are built to professional quality standards to withstand tough use in commercial and industrial settings. For everything from load measurement to troubleshooting industrial motors and adjustable speed drives (ASDs), the new TightSight® brings speed, accuracy, safety and ease-of-use together in one rugged meter line.



SAFETY

- The patented TightSight® display lets you easily take readings while keeping your head at a safe distance from the panel— no more need to twist the meter or risk pulling on an energized conductor
- Easy to read backlit displays with large numbers and icons so you can always see the correct reading



PRODUCTIVITY

- Read and record while clamped versus holding the reading, unclamping, moving and recording
- Hook tip for easier wire separation and tapered jaws for reaching into tight spaces
- True RMS provides accurate readings in electrically noisy environments
- Broad current range from 0 to 1000 amps (61-770 series) covers multiple applications
- Large jaw diameter for cables up to 2" (51mm) in diameter



VALUE

- Full AC/DC capabilities: the TightSight® is equally adaptable for both AC and DC current measurement requirements – such as solar, public transportation, and battery backup applications
- Calibration services available
- 2-year warranty



Exclusive TightSight® backlit LCD Liquid Crystal Display for reading safely at a distance

No more need to twist the meter or risk pulling on an energized conductor. The patented TightSight® display lets you easily read the bottom display while keeping your head at a safer distance from the panel.

Measure circuit current in confined and hard to reach locations!

The TightSight® allows you to safely and easily view the current measurement due to the exclusive LED backlit TightSight® LCD display located on the bottom of the clamp meter.



Tapered jaws with hook tip for tight locations and easy wire separation

CAT III
1000V

CAT IV
600V

Data hold button and offset thumb wheel for one-handed operation

Large numbers and symbols are easy to read

Exclusive TightSight® prevents you from having to lean into the panel to view the display AND helps prevent you from tugging on a live conductor.

660 AAC
No. 61-763 ▶



660 AAC/ADC
No. 61-765 ▶



1000 AAC
No. 61-773 ▶



1000 AAC/ADC
No. 61-775 ▶

