



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948



621144R1 2 20W, Led BLK Large Up and Down Sconce 120/277V

Satco

Catalog Number	621144R1
Manufacturer	Satco
Description	2 Light Led Large Up and Down Sconce Fixture - Black Finish 20W 120/277V
Weight per unit	3.2 (lbs/each)
Product Category	Led Wall Mounted Architectural

Features

beam angle	40
Lamp Included	Integrated
Lamp Type	LED
lumens	1800
Material	Die Cast Aluminum
Number of Lamps	2
Socket Type	Integrated
Voltage Rating	120/277
Warranty	5 Year Limited - Fixtures
Wattage	20

Material, Color, and Finish

Color	Black
color temperature	3000
fixture material	die-cast aluminum
Style	Utility

Dimensions and Weight

Height	11.69
Length	3.35
Width	4.53

Descriptions

Description	2 20W, LED BLK LARGE UP AND DOWN SCONCE 120/277V
extra long description	SATCO 62/1144R1 2 LT LED LG UP DOWN
Long Description	2 Light LED Large Up and Down Sconce Fixture - Black Finish 20W 120/277V
Product Type	2 LT Led LG Up Down Sconce 20W BK
Special Features	Warranty: 5-Years ; Installation Notes: Mounts Up and Down ; FCC Compliant: True ; Photo Cell: No Photocell ; Cct Selectable: False ; CCT (Kelvin Temp): 3000K ; Hours Rated: 50000 ; Beam Angle (degree): 40 ; Indoor Outdoor: Outdoor ; IP Rating: IP65 ; Operating Temp: -30C (-22F) to +50C (+122F) ; Watts: 20W ; Lumens: 1800L



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948

Manufacturer Information

Brand	NUVO LIGHTING
GTIN	00045923680908
Manufacturers Part Number	62/1144R1
UPC	045923680908

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	LED Decorative

Packaging

Carton	1
Weight	2.51
Weight Per each	3.17

Uses, Certifications, and Standards

Application	Outdoor
Frequency Rating	50/60
Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
standard	cULus - Certified