

# Eaton 6269HGC

Catalog Number: 6269HGC

Eaton Arrow Hart safety grip hospital grade straight blade connector, #18-12 AWG, 15A, Industrial, 125V, Back wire, Clear, Brass, Nylon, 5-15P, Two-pole, three-wire, grounding, Screw, Nylon, Core pack



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart safety grip hospital grade straight blade connector	6269HGC
	<b>UPC</b>
	040893052199
<b>Product Length/Depth</b>	<b>Product Height</b>
1.28 in	2.06 in
<b>Product Width</b>	<b>Product Weight</b>
1.46 in	0.195 lb
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	cULus Listed
	Federal Specification Classification W-C-596F

## Product specifications

### Device type

Connector

### Color

Clear

### Face/body material

Nylon

### Wiring method

Back wire

### Material

Nylon

### Allowable wire size

#18-12 AWG

### Amperage Rating

15A

### Number Of Poles

Two-pole

### Contact material

Brass

### Type

Connector

### Device grade

Extra heavy-duty hospital grade

### NEMA configuration

5-15P

### Style type

Straight body

### Design type

Straight blade

### Connection type

Screw

### Number of wires

3

### Receptacle type

Two-pole, three-wire, grounding

## Resources

### Brochures

[Wiring Devices Buyer's Guide](#)

### Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

### Specifications and datasheets

[Eaton Specification Sheet - 6269HGC](#)

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

Core pack



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)