



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## 63502 14" 9W Led Undercab 3K/4K/5K White

Satco



Catalog Number	63502
Manufacturer	Satco
Description	9 Watt 14-Inch Led White Under Cabinet Light - CCT Selectable - 40000 Hours
Weight per unit	0.8700 (lbs/each)
Product Category	Lighting

### Features

Lamp Type	integrated LED
Material	Aluminum and Polycarbonate (PC)
Warranty	5 Year Limited - Fixtures

### Material, Color, and Finish

Finish	white
--------	-------

### Dimensions and Weight

Height	1
Length	14
Width	3.5

### Descriptions

Description	14" 9W LED UNDERCAB 3K/4K/5K WHITE
extra long description	SATCO 63/502 UNDER CAB LED SCCT 14"
Long Description	9 Watt 14-Inch LED White Under Cabinet Light - CCT Selectable - 40000 Hours
Product Type	Under Cab Led SCCT 14" - WH
Special Features	Lumens: 576L-647L ; CCT: 3000K/4000K/5000K ; Color Temperature: Warm to Cool White ; CRI: 90+ ; Dimmable: Yes-Dimmable ; Hours Rated: 40000 ; DLC Approved: No ; Energy Star: Yes ; Warranty: 5 Year Limited - Fixtures ; Brand: CounterQuick ; ADA Compliant: Yes ; Beam Spread: 105 degrees ; CCT Selectable: Yes ; California T24 Compliant ; Incandescent Equivalent: 50W ; Indoor/Outdoor: Indoor ; IP Rating: IP20 ; NSF Approved: No ; Operating Temperature: -20C (-4F) to a maximum of +40C (+104F) ; RoHS Compliant:

### Manufacturer Information

Brand	Nuvo
GTIN	00045923656484
Manufacturers Part Number	63/502
UPC	045923656484



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING
Type	Undercabinet

## Packaging

Carton	1
Weight	0.87
Weight Per each	0.87

## Uses, Certifications, and Standards

Application	LED Undercabinet
Mounting	Undercabinet
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
standard	cETLus