



Silicone Caulk



Silicone Caulk In 10 Ounce Tubes Must Be Purchased In Case Quantity

Barcode	Catalog Number	Color	Size	Case Quantity	Price Per Tube
86004	SILICONEC	Clear	10 Ounce Tube	12	\$15.76
19801	SILICONETUBE	Clear	2.8 Ounce Tube	12	\$15.40
86006	SILICONEW	White	10 Ounce Tube	12	\$17.12

Silicone Caulk Product Info
Industrial Grade 50 Year Durability
Remains Flexible



Caulk Guns



Silicone Caulk In 10 Ounce Tubes Must Be Purchased In Case Quantity

Barcode	Catalog Number	Size	Type	Case Quantity	Price Per Each
86018	696C9	Standard	Medium Duty	12	\$11.64
19802	SCG	Standard	Heavy Duty	12	\$29.40
03988	3987	Quart	Heavy Duty	6	\$59.20

Caulk Gun Product Info
The Part SCG Is Used For Applying Fire Caulk



Plastic Pipe Cement Products



All Products Must Be Ordered In Case Quantity

Barcode	Catalog Number	Size	Color	Product Type	Case Quantity	Price Per Can
60202	60202	1/2 Pint	Clear	Cleaner	24	\$8.24
60204	60204	1 Pint	Clear	Cleaner	12	\$12.04
60215	S911P	1 Pint	Purple	PVC/CPVC Primer	12	\$18.44
60206	60206	1/2 Pint	Clear	Medium Body Cement	24	\$8.80
60210	60210	1 Pint	Clear	Medium Body Cement	12	\$14.20
60212	60212	1 Quart	Clear	Medium Body Cement	12	\$24.64
60209	LV1104MBCP	1 Pint	Clear	Low VOC Medium Body Cement	12	\$18.20
60211	LV1104MBGP	1 Pint	Gray	Low VOC Medium Body Cement	12	\$18.20
60213	LV1104MBCQ	1 Quart	Clear	Low VOC Medium Body Cement	12	\$30.40
60214	LV1104MBGQ	1 Quart	Gray	Low VOC Medium Body Cement	12	\$30.40

Plastic Pipe Product Info
For Use On PVC Conduit Types I & II Up To & Including 6" For Schedule 40 & 80
For Use In Electrical Conduit Applications Only
Low VOC Product Meets California Requirements



Insulating Foam Sealant



Insulating Foam Must Be Ordered In Case Quantity

Barcode	Catalog Number	Size	Case Quantity	Price Per Tube
86002	FOMO24	12 oz	12	\$17.40



Wipers Towels & Rags



DYNA-WIPES Must Be Purchased In Case Quantity

Barcode	Catalog Number	Color	Type	Size	Package Size	Case Quantity	Price Per Package
59472	D763-8	White	DYNA-WIPES Wet Wipes	9" x 12"	80	8	\$51.20
99953	KC41041	Blue	Paper Product	12.5" x 16.8"	160	1	\$114.20
99954	KC34015	White	Paper Product	12.5" x 16.8"	180	1	\$71.80
64016	640-16	White	Recycled Knit	N/A	1 LB	20	\$10.00
34010	340-10	White	Recycled Knit	N/A	10 LB	1	\$71.60

Wipers Towels & Rag Product Info

DYNA-WIPES Wet Wipes Will Remove Grease, Permanent Marker, Paints, Urethane, & PVC Cement. DYNA-WIPES, Can Be Thrown Away Just Like A Paper Towel. No Hazardous Materials.



Cold Galvanizing Spray



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Case Quantity	Price Per Can
16858	1685830	6	\$20.60

Cold Galvanized Spray Product Info
Industrial Grade 50 Year Durability



Spray Paint



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Color	Case Quantity	Price Per Can
24049	V2402830	Black	6	\$9.00
24039	V2403830	White	6	\$9.00
24079	V2407830	Red	6	\$9.00
24099	V2409830	Yellow	6	\$9.00
24149	V2414830	Orange	6	\$9.00
24139	V2413830	Machine Gray	6	\$9.00



Inverted Marking Paint



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Color	Case Quantity	Price Per Can
11267	203029	Safety Red	12	\$15.96
16628	1662838	Fluorescent Red	12	\$15.96
11266	203028	Fluorescent Red-Orange	12	\$15.96
11263	203025	Hi Vis Yellow	12	\$15.96
11265	203027	Fluorescent Orange	12	\$15.96
11268	203030	White	12	\$15.96
11260	203022	Caution Blue	12	\$15.96
16618	203023	Fluorescent Green	12	\$15.96
61838	1661838	Fluorescent Pink	12	\$15.96
16698	1669838	Fluorescent Purple	12	\$15.96
16019	1601838	Clear	12	\$15.96

Inverted Marking Paint Product Info

No Mess Spray Tip Keeps Paint Off Fingers & Is Guaranteed Not To Clog
Dries Fast With No Premature Fading



Cleaners & Degreasers



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
20385	ICA366	Safety Solvent CT	20 oz - Net 18 oz	02018, 02069, 02180	12	\$27.76

Safety Solvent CT Product Info

This Product Is One Of The Most Powerful Electronics/Electrical Industrial Solvent Cleaners Available.
It Is Fast Drying, Nonflammable, Nonconductive & Completely Non-Ozone Depleting.
The Low Odor Dual Action Spray Valve Allows A Mist Or Blast
Non Conductive To 29,000 Volts
Not Recommended For Prolonged Contact With Plastic

Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
20438	ICA123	Glass Cleaner	20 oz - Net 19 oz	14412	12	\$11.72

Glass Cleaner Product Info

This aggressive & Versatile Glass Cleaner Is Specially Formulated For Outdoor & Indoor Glass Surfaces.
Quickly Dissolves Smudge, Film, Scum, Smear, Bug Residue & Other Stubborn Soils. The Foaming Nonammoniated
Formula Does Not Streak & Is Safe For Use On Window Tinting, Clear Plastic, Mirrors & Other Glass Surfaces.
360 Degree Valve Allows Can To Spray Upside Down



**Looking For New Counter Merchandising Opportunities?
Talk To Your Peco Sales Person About A Point Of Purchase
Chemical Display.**



Electronics Cleaners



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
20384	ICA363	Electronics Cleaner AF	16 oz - Net 14 oz	02016	12	\$46.28

Electronics Cleaner AF Product Info

Removes Oil, Dirt, Condensation & Moisture From Circuit Boards, Precision Instruments, Oxygen Equipment, Controls, Switches, & Electrical Motors. Approved For Short-Term Contact On A Wide Variety Of Component Plastics Such As: Acetal, Neoprene, Nylon, Polyethylene (HDPE), Polyphenylene Sulfide (PPS), Polypropylene (copolymer), Polysulfane, Teflon, & Viton. Leaves No Residue & Is Compatible With Many Component Metals Such As Steel, Brass, Copper, Nickel, Tin, Titanium, & Zinc.
Fast Dry Nonflammable Electronics Cleaner & Will Not "Freeze Out"
Nonconductive To 12,000 Volts

Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
20409	ICA368	Electronics Cleaner DF	16 oz - Net 11 oz	02130	12	\$22.88

Electronics Cleaner DF Product Info

This Fast Drying, Nonconductive, Formulation Leaves No Residue & Is Compatible With Component Plastics, Rubber & Metal. This Next Generation Product Contains No CFC's, HCFC's, Or Other Ozone Depleters. Blasting Spray Easily Cleans Oil, Flux, Dirt & Other Contaminants From Contacts, Printed Circuit Boards, Switches, Electric Motors & Electronic Precision Instruments. While Advanced In Performance & Ozone Safety, This Product Is Flammable & Must Therefore Be Used Only On De-energized Components & Equipment. Always Allow To Dry & Evacuate Fumes Before Power Is Returned.
Nonconductive Up To 25,000 Volts

Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
10361	ICA361	Dual Purpose Blaster	12 oz - Net 7 oz	14085	12	\$29.40

Dual Purpose Blaster Product Info

The Product Utilizes The Highest Purity Nonflammable HFC Material To Create A Nonresidue Formula That Is Completely Plastics Safe & Contains No Ozone Depleters. The Blasting Spray Quickly & Easily Removes Dirt & Dust From Surfaces Including Contacts, Circuit Boards, Micro-Components, Relays, Print Heads, & Monitors. It is Ideally Suited For The Maintenance Of All Electronic Or Electrical Devices In Industry From Computers & Office Equipment To Industrial Machinery & Manufacturing Equipment.



Specialty Aerosols



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
20381	ICA437	Wasp & Hornet Killer	20 oz - Net 13.5 oz	14010	12	\$21.20

Wasp & Hornet Spray Product Info

Drops Wasps, Hornets, & Yellow Jackets Instantly. Kills With Residual Action As Wasps & Hornets Return To Nest. Jet Spray Will Reach Nests Up To 20 Feet Above Ground. Contains Synergis Piperonyl Butoxide, Permethrin And Tetramethrin Dielectric Breakdown Voltage Of 47,300 Volts. Can Be Used Both Indoors & Outdoors.
Solvent Based Insecticide
Nonflammable & Nonconductive To 47KV



Specialty Aerosols



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
00482	ICA482	Insect Repellant	6 oz - Net 5 oz	14011	12	\$23.80

Insect Repellant Product Info

Repels Mosquitos, Chiggers, Ticks, Biting Flies, & Other Small Flying Insects Including Fleas On Exposed Skin.
23.75% D.E.E.T. For Greater Insect Repelling



Lubricants & Penetrants



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
00391	ICA391	Multipurpose Lubricant	16 oz - Net 15 oz	02061, 03045	12	\$21.20

Multipurpose Lubricant Product Info

This Nonflammable Lubricant Is A Combination Of Special Water Displacement Compounds, Corrosion Inhibitors, Solvents, Non-Greasy Lubricants & PTFE. It Is Used To Displace Water & Moisture From Electrical Equipment Such As Contact Points & Automotive Distributors, & Machinery Parts.
Nonflammable 4N1 For Superior Rust Control
Excellent Rust Buster

Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
00392	ICA392	Penetrating Lubricant EF	16 oz - Net 12 oz	03045	12	\$19.80

Penetrating Lubricant EF Product Info

This Advanced Technology 4-N-1 Product Is Made With Cerflon For High Performance In A Nondrying Oily Film Penetrating Lubricant. The 4-N-1 Action Makes It Highly Versatile With The Ability To Penetrate, Lubricate, Displace Moisture, & Provide Superior Resistance To Corrosion. It Is Also Nonconductive To 19,000 Volts For Use Around Live Equipment. The Non-Aggressive Formula Is Safe For Use On Most Plastics & Painted Surfaces Making It An Excellent Choice For Virtually Any General Purpose Lubrication Need. The Addition Of Cerflon Not Only Improves Lubricity But Elevates Temp Range To In Excess of 500 Degrees F. Nonconductive Up To 19,000 Volts



Cutting Oil



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Size	Type	Case Quantity	Price Per Each
30201	30201	Quart	Clear	12	\$30.40
30202	30202	Gallon	Clear	6	\$70.20
30204	30204	Quart	Dark	12	\$30.40
30205	30205	Gallon	Dark	6	\$70.20

Cutting Oil Product Info

Formulated For Hand Threading Small Cutting Machines
Anti-Mist & Non-Staining Formula Is Not Affected By Weather



Cutting Oil



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Description	Size	CRC Cross Reference Number	Case Quantity	Price Per Can
00395	ICA395	Cutting Fluid	16 oz - Net 14 oz	14050	12	\$28.40

Cutting Fluid Product Info

This Product Is A Molybdenum Disulfide Formulation Which Dries To A Hard, Black Coating Very Quickly. It Adheres To Many Substrates, Especially Metal, With Minimal Surface Preparation. It Resists Wear & Abrasion, Provides High Lubricity, Gives Excellent Extreme-Pressure Properties & Is Stable At Extreme Temperatures, Both High & Low. Typical Applications For This Lubricant Are Chain Lubricating, Maintenance On Furnaces, Kilns, Ovens, Conveyers, Gasket Coatings, Anti-Seize, & Mold Releases, Etc. Contains No Chlorinated Solvents Or Ozone Depleters & Is Ideal For Use Throughout General Industry.
Nonflammable & Nonchlorinated



Residential Fireblock Sealant Foam



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Color	Size	Case Quantity	Price Per Can
20192	P10192	Orange	24 ounce	12	\$50.40

Fireblock Product Info

Designed to Seal, Fill, Bond & Stop Air Infiltration In Residential Construction
More Effective Than Traditional Fireblock Materials At Blocking Smoke
One 24 Ounce Can Replaces Up To 30 Standard Tubes Of Caulk
Orange Color Allows Inspectors To Easily Identify The Use Of A Fireblock Product



Fire Stop Products



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Size	Description	Case Quantity	Price Per Tube
66382	MC66382	10.3 oz	MC150+ Elastomeric Firecaulk	24	\$27.76

MC150+ Elastomeric Firecaulk Product Info

Metacaulk 150+ Is A General Purpose Fire-Rated Sealant & Smoke Seal For Construction Joints & Through-Penetrations. MC150+ Can Be Used On Various Penetrations Such As Top Of Wall Construction Joints, EMT, Telephone, & Power Cables In Concrete Floors & Walls, Gypsum Walls As Well As Wood Floors.
MC150+ May Be Applied With a Caulking Gun Or Trowel.
Water Based, Non-Sag Caulking Grade Sealant

Must Be Purchased In Case Quantities

Barcode	Catalog Number	Size	Description	Case Quantity	Price Per Tube
66610	MC66610	10.3 oz	350I Intumescent Firecaulk	24	\$37.28

350I Intumescent Firecaulk Product Info

Metacaulk 350I Is An Intumescent General Purpose Fire-Rated Sealant & Smoke Seal For Construction Joints & Through-Penetrations. 350I Cures to Elastomeric Seal That Is Suitable Where Dynamic Movement Is Expected.
Water Based, Non-Sag Caulking Grade Sealant

Chemicals



Fire Stop Products



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Size	Description	Case Quantity	Price Per Tube
66302	MC66302	10.3 oz	1000 Intumescent Firecaulk	24	\$44.40

1000 Intumescent Firecaulk Product Info

Metacaulk 1000 Is A General Purpose, Fire-Rated Sealant For Through-Penetrations On Both Vertical & Horizontal Surfaces, As Well As Construction Joints. It Is Designed For Use In Floors Or Walls & Can Be Used On PVC, CPVC, ABS, PVC Foam Core, ABS Foam Core, PP or Plastic Pipes, Polybutylene (PB), Insulated & Uninsulated Steel Pipe, Copper, & Cast Iron.

Must Be Purchased In Case Quantities

Barcode	Catalog Number	Size	Description	Case Quantity	Price Per Tube
66345	MC66345	5" x 11" x 8"	Putty Stick - 18 Cubic Inches	12	\$75.20

Putty Stick Product Info

Putty Sticks Are Used To Seal Around Penetrating Items Through Fire Rated Walls, Floors, & Within Blank Openings. For Use With Electrical Cables, Conduit, & Metal Pipes. Hand Moldable With No Cure Time Required. Will Not Dry Out & Can Be Re-Used As Additional Penetrating Items Are Removed Or Added.

Must Be Purchased In Case Quantities

Barcode	Catalog Number	Size	Description	Case Quantity	Price Per Tube
66340	MC66340	1/8" x 6" x 7"	Putty Pad	20	\$17.44
66335	MC66335	1/8" x 7" x 7"	Putty Pad	20	\$19.52

Putty Pad Product Info

Putty Pads Are Used To Maintain The Hourly Rating Of Fire Rated Walls Containing Electrical Outlet Boxes And To Reduce Sound Transmission. Only One Pad Thickness (1/8") Is Required For A 1 Or 2 Hour Fire Rating. No Additional Putty Material Is Needed To Plug The End Of Each Electrical Conduit At It's Connection To The Box.



Duct Seal



Barcode	Catalog Number	Size	Case Quantity	Price Per Each
60400	DS-1	1 LB	50	\$6.40
60405	DS-5	5 LB	10	\$27.40

Duct Seal Product Info

Designed to Seal Around Junction Boxes, Service Entrances, and other Areas Where An Air Tight & Water Tight Seal Are Needed



**See Section 7
For Box & Cover Gaurds**





Leak Stopper Rubberized Roof Patch



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Size	Package Type	Case Quantity	Price Per Each
03190	0319-GA	10 oz	Caulk Tube	12	\$16.48
03180	0318-GA	Quart	Can	12	\$19.84
33110	0311-GA	Gallon	Can	6	\$51.60

Leak Stopper Product Info
 Stops Roof Leaks Instantly
 Rubberized To Prevent Cracking – 10 Year Product



Lightweight Spackling



Must Be Purchased In Case Quantities

Barcode	Catalog Number	Size	Case Quantity	Price Per Each
00542	RD542	1/2 Pint	12	\$11.92
00544	RD544	Quart	6	\$29.40
00541	RD541	Gallon	2	\$68.88



Plastic Putty Knife



Barcode	Catalog Number	Size	Case Quantity	Price Per Each
04712	RD4712	2"	36	\$2.52

Notes

Chemicals