

Eaton 6450W-BU

Catalog Number: 6450W-BU

Eaton heavy-duty industrial specification grade decorator single receptacle, #14-10 AWG, 20A, Commercial, Flush, 250V, Back and side, White, Brass, Nylon, 5-20R, Single, Screw, Nylon, Bulk



General specifications

Product Name	Catalog Number
Eaton heavy-duty industrial specification grade decorator single receptacle	6450W-BU
	UPC 032664584107
Product Length/Depth	Product Height
1.32 in	4.19 in
Product Width	Product Weight
0.84 in	0.15 lb
Warranty	Certifications
Refer to warranty document.	UL Federal Specification Classification 6233 01

Product specifications

Device type

Receptacle

Color

White

Face/body material

Nylon

Wiring method

Back and side

Features

Auto-grounding

Material

Nylon

Mounting method

Flush

Allowable wire size

#14-10 AWG

Amperage Rating

20A

Number Of Poles

Two-pole

Contact material

Brass

Type

Decorator single receptacle

Device grade

Heavy-duty industrial specification grade

NEMA configuration

5-20R

Style type

Decorator

Design type

Straight blade

Connection type

Screw

Number of wires

Resources

Brochures

[Spec grade receptacles brochure](#)

Catalogs

[Arrow Hart Buyers Guide Section A](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 6450W-BU](#)

3

Receptacle type

Single

Voltage rating

250V

Application

Commercial

Torque rating

14 lbf-inch

Packaging type

Bulk



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)