ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



65220 LED SECURITY FLOOD W/O SENSOR - BLACK

SATCO

Catalog Number	65220
Manufacturer	SATCO
Description	LED Security Light - Dual Head Black Finish 4000K
Weight per unit	2.5 (lbs/each)
Product Category	Security Lights

Features

Ballast Type	Self
Lamp Type	LED
Material	Die Cast Aluminum
Number Of Lamps	2
Power Rating	0.9
Reflector Type	Frost
Socket Type	Integrated
Voltage Rating	120 to 277
Warranty	5 Year Limited - Fixtures
Wattage	20
Amperage Rating	0.200 to 0.072

Material, Color, and Finish

Style	Utility
Fixture Material	die-cast aluminum

Dimensions and Weight

Height	7.63
Length	7.63
Size	L:7.63 W:4.16 H:4.13
Width	4.16

Descriptions

Description	LED SECURITY FLOOD W/O SENSOR - BLACK
Long Description	LED Security Light - Dual Head Black Finish 4000K
Product Type	Led Dual Head Security Light
Special Features	Warranty: 5-Years ; FCC Compliant: True ; Cct Selectable: False ; CCT (Kelvin Temp): 4000K ; Hours Rated: 50000 ; Beam Angle (degree): 50 ; Indoor Outdoor: Outdoor ; IP Rating: IP65 ; Lens Finish: Frost ; Lens Material: Glass ; Operating Temp: -30C (-22F) to +50C (+122F) ; Watts: 20W ; Lumens: 1900L
Extra Long Description	SATCO 65/220 LED DUAL HEAD SECURITY

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	Satco
	Nuvo
GTIN	00045923680427
Manufacturers Part Number	65/220
UPC	885860

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Commercial LED

Packaging

Carton	1
Weight	2.54
Weight Per Each	2.5 (lbs/each)

Uses, Certifications, and Standards

Application	Outdoor
Frequency Rating	50/60
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Environmental Conditions	Wet
Standard	cULus - Certified

Project Name

Location

Prepared By



NUVO 65-220

LED DUAL HEAD SECURITY LIGHT

Notes

[www] 10-11-2021 02:06:28

General

Status	Active
Fixture Type	Security Lighting
Finish	Black
Wattage	20W
Lumen Output	1900L
CCT (Kelvin)	4000
Temperature	Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	80
Voltage	100V-277V
Beam Angle	50
Rated Hours	50000
Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
Dimmable	Non-Dimmable
Lens Material	Glass
Weight (lb.)	2.54
Material	Die Cast Aluminum

Dimensions

Width (in.)	4.16
Length (in.)	7.63

Compliance

Safety Listing	cULus
Location Rating	Wet
UL Application	Outdoor
Energy Star	Yes
ES Unique ID	ESID-2336405
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
http://www.satco.com/