



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

65716 Led Double Head Security Light 40K WHT (No Sensor)

Satco



Catalog Number	65716
Manufacturer	Satco
Description	Led Security Light - Dual Head - White Finish - 4000K
Weight per unit	2.5 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED
Material	Die Cast Aluminum
Number of Lamps	2
Socket Type	Hardwired
surge protection	Built-in surge protection - 2KV
Voltage Rating	277
Warranty	5 Year Limited - Fixtures

Material, Color, and Finish

fixture material	die-cast aluminum
Style	Flood Light

Descriptions

Description	LED DOUBLE HEAD SECURITY LIGHT 40K WHT (NO SENSOR)
extra long description	SATCO 65/716 LED 2 BULLET HEAD SECU
Long Description	LED Security Light - Dual Head - White Finish - 4000K
Product Type	Led 2 Bullet Head Security LGT WH 40K
Special Features	Watts: 20W ; Volts: 120V-277V ; Lumens: 1900 ; Color temperature: 4000K Cool White ; CRI: 80 ; Non-Dimmable ; Average rated hours: 50000 ; Warranty: 5 Year Limited - Fixtures ; Beam spread: 50 degrees ; California T24 2016 & 2019 JA8 Compliant - Outdoor LED ; HID equivalent: 70W ; Incandescent equivalent: 125W ; Operating temperature: -30C (-22F) to a maximum of +50C (+122F) ; IP rating: IP65

Manufacturer Information

Brand	Satco
GTIN	00045923629556
Manufacturers Part Number	65/716
UPC	045923629556



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
----------------------	-----------------------------------------------------------

Type	Dual Head
------	-----------

Packaging

Carton	1
--------	---

Weight	2.41
--------	------

Weight Per each	2.54
-----------------	------

Uses, Certifications, and Standards

Application	OUTDOOR LIGHTING
-------------	------------------

environmental conditions	Outdoor Wet Location
--------------------------	----------------------

Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
-----------------------	------------------------------------------

standard	cETLus
----------	--------