

## TradeMaster Grounding Toggle Switch, Ivory

660IG



Single Pole Switch in ivory, with grounded terminals, is made of a thermoplastic toggle and frame. It has a smooth, quiet toggle action. It is made with high-impact resistant construction. 15 amps, 120 volts.

\*Available in bulk packs of 120. Add "U" to end of Catalog Number. Example: 660IGU

### features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.

### specifications

#### General Info

Product Series: TradeMaster  
Type: Toggle  
Number Of Poles: 1  
Special Features: Self-Grounding

#### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
UL Listing No: UL20  
UL Standard: Yes  
UN SPS C: 39121406

**Dimensions**

Depth U S: 1.090"  
Height U S: 3.281"  
Width U S: 1.25"

**Technical Information**

Amps: 15 Amp  
Volts: 120VAC  
Volts A C: 120

**Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: Trade Agreement Act Compliant