

TradeMaster Grounding Toggle Switch, Light Almond

660LAG



features & benefits

Single Pole Switch in light almond with grounded terminals, is made with a thermoplastic toggle and frame. It has a smooth, quiet toggle action. It is made with high-impact resistant construction. 15 amps, 120 volts.

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.

*Available in bulk packs of 120. Add "U" to end of Catalog Number. Example:
660LAGU

specifications

General Info

Product Series: TradeMaster
Type: Toggle
Number Of Poles: 1
Special Features: Self-Grounding

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111
CSA Standard: Yes
UL Listing No: UL20

UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: 1.090"
Height U S: 3.281"
Width U S: 1.25"

Technical Information

Amps: 15 Amp
Volts: 120VAC
Volts A C: 120

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: Trade Agreement Act Compliant