Stylus Pro® Alkaline Battery-Powered LED Pen Light

Case Material: Corrosion & water resistant, machined aircraft-grade aluminum alloy, Type II MIL-Spec anodize plating.

Dimensions: Length: 5.3"; 134 mm Body Diameter: 0.6"; 15 mm

Weight: 1.64 oz.; 46.9 grams with battery (AAA Panasonic battery included with purchase)

Light Source: 0.5 Watt High-Flux LED; 30,000 hour LED life

Light Output: Up to 24 lumens

On/Off: Push button tail switch

Run Time: Up to 7.5 hours of regulated runtime

Battery: Two (2) "AAA" alkaline batteries

Features: • Proprietary Micro Optical System (MOS), for optimized output and runtime

"Battery-Booster" electronics provide a super-bright beam
An internal polymer body liner and about proof switch

 An internal polymer body liner and shock proof switch housing allow for operation under the most extreme conditions

• Water resistant per IPX4; in accordance with specification EN 60529:1992

• Shock-proof; drop test verified above the industry standard of six feet

• Type II MIL-SPEC abrasion and corrosion-resistant anodized aircraft aluminum

Rubber push button tail cap switch

O-ring sealed

• Unbreakable polycarbonate lens

· Holster - inlcuded in package

· Unbreakable pocket clip

Approvals: Most models meet applicable European Community Directives.

Warranty: Limited lifetime warranty.

Made in China



| Item | | UPC | Part# |
|------------|-----------------------|----------------|-------|
| Stylus Pro | Black with White LED | 080926-66118-9 | 66118 |
| Stylus Pro | Blue with White LED | 080926-66122-6 | 66122 |
| Stylus Pro | Silver with White LED | 080926-66121-9 | 66121 |
| Stylus Pro | Red with White LED | 080926-66120-2 | 66120 |



