

Eaton 6612 G NK

Catalog Number: 6612 G NK

Eaton B-Line series wiring trough, 6" height, 12" length, 6" width, G NK wireway, Thru holes, No knockouts, Screw cover, NEMA 1, Steel, Plated screws, ANSI 61 gray, 16 gauge

General specifications



Product Name	Eaton B-Line series wiring trough	Catalog Number	6612 G NK
UPC	782051001532	Product Length/Depth	12 in
Product Height	6 in	Product Width	6 in
Product Weight	4.814 lb	Certifications	CSA Certified UL Listed

Photo is representative

Material/finish

Material thickness

16 gauge

Finish color

ANSI 61 gray

Model

Closure type

Plated screws

Mounting method

Thru holes

Special features

Cover is secured with plated screws

Type

G NK wireway

Resources

Catalogs

[EnviroShield Wireway Flyer](#)

Specifications and datasheets

[Eaton Specification Sheet - 6612 G NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)