



**MILBANK**<sup>®</sup>  
ENERGY AT WORK



## 6624-GHC1-NK

Catalog Number	6624-GHC1-NK
Marketing Product Description	6x24X6 Hinge Cover Wireway Type 1 UL Listed Steel No Knockouts ANSI 61 Gray
UPC	784572107854
Length (IN)	24
Width (IN)	6
Height (IN)	6
Weight (LB)	10.5
Brand Name	Milbank
Type	Lay In Wireway
Application	Wireway
Standard	UL Listed
Cover Type	Hinge Cover
Enclosure	Indoor Enclosure
Nominal Cross Section	6x6
Straight Section Length	24
Material	Steel
Finish	ANSI 61 Gray Powder Coat Finish
Knockouts	False
NEMA Rating	Type 1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



**MILBANK**<sup>®</sup>  
ENERGY AT WORK

## 6624-GHC1-NK



Catalog Number	6624-GHC1-NK
Marketing Product Description	6x24X6 Hinge Cover Wireway Type 1 UL Listed Steel No Knockouts ANSI 61 Gray
UPC	784572107854
Length (IN)	24
Width (IN)	6
Height (IN)	6
Weight (LB)	10.5
Brand Name	Milbank
Type	Lay In Wireway
Application	Wireway
Standard	UL Listed
Cover Type	Hinge Cover
Enclosure	Indoor Enclosure
Nominal Cross Section	6x6
Straight Section Length	24
Material	Steel
Finish	ANSI 61 Gray Powder Coat Finish
Knockouts	False
NEMA Rating	Type 1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.