



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2646 SE Washington Blvd
74006-0000, OK Bartlesville
Phone: 918-876-3357
Fax: 918-876-3358



6636GRTNK 6X6X36 Nema 3R Gutter *Unity Manufacturing*

| | |
|------------------|--|
| Catalog Number | 6636GRTNK |
| Manufacturer | Unity Manufacturing |
| Description | Slip-On Cover Trough, Slip On, Gray, Low Carbon Steel, 36 In Overall Length, 6 In Overall Height, 6 In Overall Width, Powder Coated, 16 LB |
| Weight per unit | 16.0 (lbs/each) |
| Product Category | Nema Type 3R Trough & Gutter |

Features

| | |
|-----------|----|
| Knockouts | NO |
|-----------|----|

Dimensions and Weight

| | |
|--------|----|
| Depth | 6 |
| Length | 36 |
| Width | 6 |

Descriptions

| | |
|------------------------|--|
| Description | 6X6X36 NEMA 3R GUTTER |
| extra long description | UNT 6636GRTNK 36.00 X 6.00 X 6.00IN |
| Special Features | For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Unity |
| GTIN | 00761515141977 |
| UPC | 761515141977 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | GRT Gutter Slip-On Cover Wiring Trough |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Package | 2 |
| Weight Per each | 16 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2646 SE Washington Blvd
74006-0000, OK Bartlesville
Phone: 918-876-3357
Fax: 918-876-3358

Uses, Certifications, and Standards

Enclosure
standard

NEMA 3R, IP32

UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily
To Provide A Degree Of Protection Against Rain, Sleet And
Damage From External Ice Formation, CSA C22.2 No. 26 Certified,
Type 3R, IEC 60529, RoHS Compliant