



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832



670LAG Combo 2 Switches 1P 20A 120/277V La

Pass & Seymour/Legrand

Catalog Number	670LAG
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Double Combination Switch, 20A, 120/277V, White.
Weight per unit	0.2160 (lbs/each)
Product Category	Combination Devices

Features

action	(2) SP
actuator	Toggle
amperage rating	20
connection	Side wire
Contact Configuration	N-O
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
Load Rating	20 A @ 120/277 VAC
Load Type	LED, Incandescent, Universal, CFL, Halogen, Fluorescent, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	2.0
operating cycles	30k.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120/277 V
Voltage Rating	0.433212996389892
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	SATIN
--------	-------

Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Descriptions

Description	COMBO 2 SWITCHES 1P 20A 120/277V LA
extra long description	P&S 670LAG COMBO 2 SWITCHES 1P 20A
Features	Combination
Long Description	Single-Pole, Double Combination Switch, 20A, 120/277V, White.
Product Type	Combo 2 Switches 1P 20A 120/277V La
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007006032
Manufacturers Part Number	670-LAG
UPC	785007006032

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	COMBINATION

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.216

Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature standard	Maximum continuous +60°C, minimum -30°C CULUS, UL20