



## 15A, 120/125V COMBINATION SINGLE-POLE SWITCH & TAMPER-RESISTANT SINGLE RECEPTACLE, BROWN

691TR | [Pass & Seymour](#)

### FEATURES & BENEFITS

Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Easily accessible break-off separate or common feed.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Type: Tamper-Resistant  
Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
UL Listing No: 20, 498  
UL Standard: Yes  
UN SPSC: 39121406

#### DIMENSIONS

Depth (US): 1.15"  
Height (US): 3.81"  
Width (US): 1.32"

#### TECHNICAL INFORMATION

Amps: 15A  
NEMA Configuration Number: 5-15R  
NEMA Rating: Yes  
Volts: 120/125

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant





## 15A, 120/125V COMBINATION SINGLE-POLE SWITCH & TAMPER-RESISTANT SINGLE RECEPTACLE, BROWN

691TR | [Pass & Seymour](#)

### FEATURES & BENEFITS

Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Easily accessible break-off separate or common feed.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Type: Tamper-Resistant  
Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
UL Listing No: 20, 498  
UL Standard: Yes  
UN SPSC: 39121406

#### DIMENSIONS

Depth (US): 1.15"  
Height (US): 3.81"  
Width (US): 1.32"

#### TECHNICAL INFORMATION

Amps: 15A  
NEMA Configuration Number: 5-15R  
NEMA Rating: Yes  
Volts: 120/125

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

