



15A, 120/125V COMBINATION SINGLE-POLE SWITCH & TAMPER-RESISTANT SINGLE RECEPTACLE, WHITE

691TRW | [Pass & Seymour](#)

FEATURES & BENEFITS

Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Easily accessible break-off separate or common feed.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White

Type: Tamper-Resistant

Number Of Poles: 1

Special Features: Tamper Resistant

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UL Listing No: 20, 498

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.15"

Height (US): 3.81"

Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 120/125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant





15A, 120/125V COMBINATION SINGLE-POLE SWITCH & TAMPER-RESISTANT SINGLE RECEPTACLE, WHITE

691TRW | [Pass & Seymour](#)

FEATURES & BENEFITS

Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Easily accessible break-off separate or common feed.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White

Type: Tamper-Resistant

Number Of Poles: 1

Special Features: Tamper Resistant

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UL Listing No: 20, 498

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.15"

Height (US): 3.81"

Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 120/125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

