



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4000 Mockingbird Ln  
79109-3210, TX Amarillo  
Phone: 806-220-0404  
Fax: 806-220-0811



## 693G Combo 2 Switches 3W 15A 120/277V BN

*Pass & Seymour/Legrand*

Catalog Number	693G
Manufacturer	Pass & Seymour/Legrand
Description	Double 3-Way Combination Switch, 15A, 120/277V
Weight per unit	0.2675 (lbs/each)
Product Category	Combination Devices

### Features

action	(2) 3W
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Configuration	N-O
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
Load Rating	15 A @ 120/277 VAC
Load Type	Universal, Fluorescent, CFL, Halogen, LED, Incandescent, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	2.0
operating cycles	30k.0
Poles	3-way
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	0.433212996389892
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4000 Mockingbird Ln  
79109-3210, TX Amarillo  
Phone: 806-220-0404  
Fax: 806-220-0811

## Descriptions

Description	COMBO 2 SWITCHES 3W 15A 120/277V BN
extra long description	P&S 693G COMBO 2 SWITCHES 3W 15A 12
Features	Combination
Long Description	Double 3-way Combination Switch, 15A, 120/277V
Product Type	Combo 2 Switches 3W 15A 120/277V BN
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007006124
Manufacturers Part Number	693-G
UPC	785007006124

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Combination, Switch

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	20
Weight Per each	0.2675

## Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature standard	Maximum continuous +60°C, minimum -30°C CULUS, UL20