



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700



693W Combo 2 Switches 3W 15A 120/277V WH

Pass & Seymour/LeGrand

Catalog Number	693W
Manufacturer	Pass & Seymour/LeGrand
Description	Double 3-Way Combination Switch, 15A, 120/277V
Weight per unit	0.2500 (lbs/each)
Product Category	Combination Devices

Features

action	(2) 3W
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Configuration	N-O
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
Load Rating	15 A @ 120/277 VAC
Load Type	Halogen, Incandescent, CFL, LED, Fluorescent, Universal, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	2.0
operating cycles	30k.0
Poles	3-way
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	0.433212996389892
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700

Descriptions

Description	COMBO 2 SWITCHES 3W 15A 120/277V WH
extra long description	P&S 693WG COMBO 2 SWITCHES 3W 15A 1
Features	Combination
Long Description	Double 3-way Combination Switch, 15A, 120/277V
Product Type	Combo 2 Switches 3W 15A 120/277V W
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007006155
Manufacturers Part Number	693WG
UPC	785007006155

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Combination, Switch

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature standard	Maximum continuous +60°C, minimum -30°C CULUS, UL20