



Double 3-way Combination Switch, 15A, 120/277V

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007006155
Country Of Origin	Mexico	Material	Thermoplastic
Features	Combination	Switch Type	Toggle
Number of Switches	2	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL20
Warranty Type	1-Year Limited Warranty	Type	Combination, Switch

Dimensions

Product Width US	1.32 in	Product Depth US	0.94 in
------------------	---------	------------------	---------

Product Height US	4.06 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Load Rating	15 A @ 120/277 VAC	Contact Configuration	N-0
-------------	--------------------	-----------------------	-----

Operating Cycles	30000	Connection Location	Side Only
------------------	-------	---------------------	-----------

Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
------------------------	-------------------	-----------------	---

Throw Type	Single Throw	Amperage	15 A
------------	--------------	----------	------

Number of Poles	3-Way	Requires Neutral Wire	Yes
-----------------	-------	-----------------------	-----

Indoor/Outdoor	Indoor	Mounting Type	Wall Box
----------------	--------	---------------	----------

Wire Connection Type	Screw Terminals	Voltage	120 VAC, 277 VAC
----------------------	-----------------	---------	------------------

Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon	Environmental Conditions	Flammability: UL94 V2
-----------	---	--------------------------	--------------------------
