



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 696LAG Combo 2SW 1P+3W 15A 120/277V La

*Pass & Seymour/Legrand*

Catalog Number	696LAG
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, 3-Way Double Combination Switch, 15A 120/277V, Ivory.
Weight per unit	0.2400 (lbs/each)
Product Category	Combination Devices

### Features

action	(1) SP & (1) 3W
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Configuration	N-O
Contact Rating	15amp, 120/277vac
operating cycles	30000
Poles	1 & 3-Way
Voltage	0.433 V
Voltage Rating	0.433212996389892
Wattage	Electrical power is expressed in Amps and Volts.

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO 2SW 1P+3W 15A 120/277V LA
extra long description	P&S 696LAG COMBO 2SW 1P+3W 15A 120/
Long Description	Single-Pole, 3-way Double Combination Switch, 15A 120/277V, Ivory.
Product Type	Combo 2SW 1P+3W 15A 120/277V La
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007006223
Manufacturers Part Number	696-LAG
UPC	785007006223

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	COMBINATION



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 15.0

## Packaging

Carton ..... 10

Package ..... 50

Weight Per each ..... 0.24

## Uses, Certifications, and Standards

Application ..... Residential/Commercial

environmental conditions ..... Flammability: UL94 V2

Mounting ..... WALL

Operating Temperature ..... Maximum continuous +60°C, minimum -30°C

standard ..... CULUS, UL20