




Steel City



NOTE:
 1. MATERIAL: STAINLESS STEEL
 ALT. MATERIAL - MILD STEEL
 (CAT NO. WITHOUT SUFFIX 'SS')
 2. FINISH: AS ROLLED
 ALT. FINISH: ZINC PLATED <0.00015" THK>
 3. CAT NO WITHOUT 'B' LETTER MEANS NO BOLT.
 4. LOAD RATING IS 500 LBS WITH A SAFETY
 FACTOR OF 3 EXCEPT 6HITB, WHICH IS 400 LBS
 WITH A SAFETY FACTOR OF 3

| CAT NO | SIZE RIGID | SIZE EMT | A | B | C | D | E BOLT SIZE | F HEX NUT |
|----------|------------|----------|-------|-------|-------|-------|---------------------|-----------|
| 6H0BSS | 3/8-1/2 | 1/2 | 0.750 | 0.260 | 1.870 | 0.225 | M6-1 X 1.181" | M6-1 |
| 6H0SS | 3/8-1/2 | 1/2 | 0.750 | 0.260 | 1.870 | 0.225 | | |
| 6H0TB | 3/8-1/2 | 1/2 | 0.750 | 0.260 | 1.870 | 0.225 | 1/4"-20BSW X 1 1/4" | 1/4"-20 |
| 6H1BSS | 3/4 | 3/4 | 0.750 | 0.260 | 2.185 | 0.225 | M6-1 X 1.181" | M6-1 |
| 6H1SS | 3/4 | 3/4 | 0.750 | 0.260 | 2.185 | 0.225 | | |
| 6H2BSS | 1 | 1 | 0.875 | 0.260 | 2.520 | 0.225 | M6-1 X 1.575" | M6-1 |
| 6H2SS | 1 | 1 | 0.875 | 0.260 | 2.520 | 0.225 | | |
| 6H212BSS | - | 1-1/4 | 0.875 | 0.260 | 2.825 | 0.225 | M6-1 X 1.575" | M6-1 |
| 6H3BSS | 1-1/4 | 1-1/2 | 0.875 | 0.260 | 3.100 | 0.225 | M6-1 X 1.575" | M6-1 |
| 6H4BSS | 1-1/2 | - | 1.000 | 0.325 | 3.210 | - | M6-1 X 1.575" | M6-1 |
| 6H5BSS | 2 | 2 | 1.000 | 0.325 | 4.065 | - | M6-1 X 1.575" | M6-1 |
| 6H6BSS | 2-1/2 | 2-1/2 | 1.250 | 0.325 | 4.770 | - | M6-1 X 1.575" | M6-1 |
| 6H7BSS | 3 | 3 | 1.250 | 0.325 | 5.340 | - | M6-1 X 1.575" | M6-1 |
| 6H8BSS | 3-1/2 | 3-1/2 | 1.250 | 0.325 | 5.950 | - | M6-1 X 1.575" | M6-1 |
| 6H9BSS | 4 | 4 | 1.250 | 0.325 | 6.355 | - | M6-1 X 1.969" | M6-1 |
| 6HITB | 3/4 | 3/4 | 0.750 | 0.260 | 2.185 | 0.225 | 1/4"-20BSW X 1 1/4" | 1/4"-20 |

GENERAL NOTES

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

- | | |
|---|--|
| 2 | SEE ERN (2015491) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: 015V000377 |
|---|--|

www.tnb.com

Thomas & Betts

A Member of the ABB Group

DESCRIPTION:

HANGER FOR RIGID CONDUIT EMT WITH CLAMP SCREW

ORIGINAL PROJECT NO / (ERN NO)

015V000377 / (2014410)

SHEET NO:

1 OF 1

REV. NO:


2

DRAWING NO:

WSD-001108



Steel City

**NOTE:**

1. MATERIAL: STAINLESS STEEL
ALT. MATERIAL - MILD STEEL
(CAT NO. WITHOUT SUFFIX 'SS')
2. FINISH: AS ROLLED
ALT. FINISH: ZINC PLATED <0.00015" THK>
3. CAT NO WITHOUT 'B' LETTER MEANS NO BOLT.
4. LOAD RATING IS 500 LBS WITH A SAFETY FACTOR OF 3 EXCEPT 6HITB, WHICH IS 400 LBS WITH A SAFETY FACTOR OF 3

| CAT NO | SIZE RIGID | SIZE EMT | A | B | C | D | E BOLT SIZE | F HEX NUT |
|----------|------------|----------|-------|-------|-------|-------|---------------------|-----------|
| 6H0BSS | 3/8-1/2 | 1/2 | 0.750 | 0.260 | 1.870 | 0.225 | M6-1 X 1.181" | M6-1 |
| 6H0SS | 3/8-1/2 | 1/2 | 0.750 | 0.260 | 1.870 | 0.225 | | |
| 6H0TB | 3/8-1/2 | 1/2 | 0.750 | 0.260 | 1.870 | 0.225 | 1/4"-20BSW X 1 1/4" | 1/4"-20 |
| 6H1BSS | 3/4 | 3/4 | 0.750 | 0.260 | 2.185 | 0.225 | M6-1 X 1.181" | M6-1 |
| 6H1SS | 3/4 | 3/4 | 0.750 | 0.260 | 2.185 | 0.225 | | |
| 6H2BSS | 1 | 1 | 0.875 | 0.260 | 2.520 | 0.225 | M6-1 X 1.575" | M6-1 |
| 6H2SS | 1 | 1 | 0.875 | 0.260 | 2.520 | 0.225 | | |
| 6H212BSS | - | 1-1/4 | 0.875 | 0.260 | 2.825 | 0.225 | M6-1 X 1.575" | M6-1 |
| 6H3BSS | 1-1/4 | 1-1/2 | 0.875 | 0.260 | 3.100 | 0.225 | M6-1 X 1.575" | M6-1 |
| 6H4BSS | 1-1/2 | - | 1.000 | 0.325 | 3.210 | - | M6-1 X 1.575" | M6-1 |
| 6H5BSS | 2 | 2 | 1.000 | 0.325 | 4.065 | - | M6-1 X 1.575" | M6-1 |
| 6H6BSS | 2-1/2 | 2-1/2 | 1.250 | 0.325 | 4.770 | - | M6-1 X 1.575" | M6-1 |
| 6H7BSS | 3 | 3 | 1.250 | 0.325 | 5.340 | - | M6-1 X 1.575" | M6-1 |
| 6H8BSS | 3-1/2 | 3-1/2 | 1.250 | 0.325 | 5.950 | - | M6-1 X 1.575" | M6-1 |
| 6H9BSS | 4 | 4 | 1.250 | 0.325 | 6.355 | - | M6-1 X 1.969" | M6-1 |
| 6HITB | 3/4 | 3/4 | 0.750 | 0.260 | 2.185 | 0.225 | 1/4"-20BSW X 1 1/4" | 1/4"-20 |

GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

- | | |
|---|---|
| 2 | SEE ERN (2015491) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: 015V000377 |
|---|---|

www.tnb.com

Thomas & Betts

A Member of the ABB Group

DESCRIPTION:

HANGER FOR RIGID CONDUIT EMT WITH CLAMP SCREW

ORIGINAL PROJECT NO / (ERN NO)

015V000377 / (2014410)

SHEET NO:

1 OF 1

REV. NO:

2

DRAWING NO:

WSD-001108