



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

71333C 36W/48W/60W 3K/4K/5K Barn Light With Short Cap

Morris Products Inc.



| | |
|------------------|--|
| Catalog Number | 71333C |
| Manufacturer | Morris Products Inc. |
| Description | Led Area Light Fixture, Powder Coated Gray Finish; UI (Canada and Us), DLC Approval; Bracket Mounting; Led Lamp Type; 50 Watt Lamp Wattage; Die-Cast Aluminum Housing Material; 120/208/240/277 Volt Ac Lamp/Ballast Voltage |
| Weight per unit | 7.5 (lbs/each) |
| Product Category | Led Roadway Lighting |

Features

| | |
|----------------------|---------------------------------------|
| Control Type | Twist Lock Photocell |
| Lamp Type | LED |
| Lamp Wattage | 50 Watt |
| Lamp/Ballast Voltage | 120/208/240/277 Volt AC |
| Reflector/Lens Type | Anti-Glare Polycarbonate Frosted Lens |

Material, Color, and Finish

| | |
|------------------|--------------------|
| Finish | Powder Coated Gray |
| Housing Material | Die-Cast Aluminum |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Additional Information | Hardware Material Stainless Steel; Enclosure Rating IP65; Current Rating 0.6 Amp; Overall Dimension 21-1/4 Inch Depth x 24 Inch Height; Intensity 5050 Lumen; Efficacy Rating 101 Lumen per Watt; Color Rendering Index 72; Color Temperature Rating 5000 Kelvi |
| Commodity Description | Led Roadway Lighting |
| Description | 36W/48W/60W 3K/4K/5K BARN LIGHT WITH SHORT CAP |
| extra long description | POWDER COATED GRAY FINISH; UL (CANADA AND US), DLC APPROVAL; BRACKET MOUNTING; LED LAMP TYPE; 50 WATT LAMP WATTAGE; DIE-CAST ALUMINUM HOUSING MATERIAL; 120/208/240/277 VOLT AC LAMP/BALLAST VOLTAGE; TWIST LOCK PHOTOCELL CONTROL TYPE; ANTI-GLARE POLYCARBONATE FROSTED LENS REFRACTOR/LENS TYPE; HARDWARE MATERIAL STAINLESS STEEL; ENCLOSURE RATING IP65; CURRENT RATING 0.6 AMP; OVERALL DIMENSION 21-1/4 INCH DEPTH X 24 INCH HEIGHT; INTENSITY 5050 LUMEN; EFFICACY RATING 101 LUMEN PER WATT; COLOR RENDERING INDEX 72; |
| Long Description | LED AREA LIGHT FIXTURE, POWDER COATED GRAY FINISH; UL (CANADA AND US), DLC APPROVAL; BRACKET MOUNTING; LED LAMP TYPE; 50 WATT LAMP WATTAGE; DIE-CAST ALUMINUM HOUSING MATERIAL; 120/208/240/277 VOLT AC LAMP/BALLAST VOLTAGE |
| Product Type | Led Area Light Fixture |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Morris Products Inc. |
| GTIN | 00601986713337 |
| Manufacturers Part Number | 71333C |
| UPC | 601986713337 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING |
|----------------------|--|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 7.5 |

Uses, Certifications, and Standards

| | |
|----------|-------------------------|
| Approval | UL (Canada and US), DLC |
| Mounting | BRACKET |