ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7145SW 14/2 100' Ul Temp Lightip

Southwire Company

Catalog Number	7145SW
Manufacturer	Southwire Company
Description	Temp Lightip, Incandescent Bulb Type, 100 FT Length, Made In Usa, 1 FT Weight
Weight per unit	0.1000 (lbs/ft)
Product Category	Lighting

Features

amperage rating	15
Lamp Type	A23 or larger
Number of Wires	1
Voltage Rating	125
Wattage	1875 max

Material, Color, and Finish

Color	Yellow

Dimensions and Weight

Size	100

Descriptions

Description	14/2 100' UL TEMP LIGHTIP
extra long description	SWC 7145SW CORD, APPLIANCE 14/2 100
Features	Southwire™ 07145 14/2 SJTW 100-Foot Temporary Light String, 1500-Watts for Indoor/Outdoor Lighting. Cord-O-Lite 100-foot extension cord with 10 lamp holders and light sockets. Evenly spaced sockets rated for bulbs up to 150-watts each, A23 or larger. Suitable for both indoor and outdoor lighting systems, Meets OSHA, NEC Requirements, UL Listed. Temporary indoor and outdoor illumination for attics, garages, unfinished construction, and more. Lampholder spacing is 10-feet, starting 9-feet from the plug - gre

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892071455
Manufacturers Part Number	071458802
UPC	029892071455

Taxonomies, Classifications, and Categories

Category Description	Incandescent (Except Residential)
Type	String Light

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per foot	0.1

Uses, Certifications, and Standards

Application	String Light
standard	UL Listed