



Core & Coil (71A) HPS ~GT~ 400W

CORE & COIL HID 71A8753001

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information				
ANSI Code	S52			
Lamp Type	1000W HPS			
Number of Lamps	1 piece/unit			
Circuit Type	CWA			
Ballast Type	Magnetic HID			
Base Model	71A8753			
Core Size	4 1/4 x 6			
Suitable For Outdoor Use	Yes			
Ignitor Catalog Number	LI571-H5			
Ignitor Temperature Rating	105°C			
Capacitor Value	26 MFD			
Capacitor Catalog Number	RW1626020			
Capacitor Requirements	525V			
Capacitor Temperature Rating	90°C			
Capacitor Diameter/Oval Dimensions	1.75 in			
Capacitor Height	4.25 in			
Automatic Restart	No			
Operating and Electrical				
Input Voltage	120/208/240/277/480 V			

Input Frequency	60 Hz
Input Current (Open Circuit)	3.9/2.19/2.01/1.71/0.96 A
Input Current (Starting)	7.8/4.38/3.82/3.3/1.9 A
Input Current (Short Circuit)	5.83-8.74/3.36-5.05/2.92-4.38/2.53-3.8/1.46-2.19 A
Secondary Short Circuit Current	6.24-7.63 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	437 V
Input Current (Nom)	9.28/5.32/4.68/4.03/2.31 A A
Input Power (Nom)	1100 W
Rated Lamp Power	1000 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	15'
Recommended Fuse Value	25/15/12/10/6 A


Datasheet, 2017, May 26 data subject to change

Core & Coil (71A) HPS ~GT~ 400W

Approval and Application	
Open Circuit Voltage Test (Volts)	390-476 V
Approval Marks	ULR CSA certificate RoHS Compliant
emperature Marking	C/C/C/C/C
JL Recognized	Yes
lipot Test (1 Minute)	2000 V
lipot Test (2 Seconds)	2500 V
JL Insulation Class	H(180°C)
UL Temperature Code	1029C

Product Data					
Order product name	CORE & COIL HID 71A8753001				
EAN/UPC - Product	781087111826				
Order code	913710405501				
Numerator - Quantity Per Pack	1				
Numerator - Packs per outer box	1				
Material Nr. (12NC)	913710405501				
Net Weight (Piece)	13.903 kg				

Dimensional drawing



HPS BAL 1000W S52 5-TAP KIT

Product	C1	C2	A1	A2	A3	B1	B2
CORE & COIL HID 71A8753001	6 in	3.97 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in

