


## Sign & scoreboard lighting

### Product description

Attachon lampholders,  
660W, 250V/AC; 200W, 250V/AC

### Features

- Insulation displacement terminals for stranded wire
- Lay in wire channels, 1/4 turn twist top speeds installation
- One piece terminals and contacts, no rivets or eyelets to loosen due to heat
- Sockets are molded of heat-resistant phenolic
- #732 is weatherproof, suitable for outdoor use
- Intermediate and candelabra bases offer snap-in or screw-in panel mounting options
- Keyed spring washer prevents rotation of socket after installation





732



732-3

### Medium base Attachon

Rating		Description	Catalog no.		
W	V/AC				
660	250	Weatherproof phenolic, wire range #14 to #12 AWG, hook mounting	□ 732	•	•
		Weatherproof phenolic, wire range #14 to #12 AWG, no hook mounting	□ 732-1	•	•
		Weatherproof phenolic, wire range #14 to #12 AWG, snap-in mounting	□ 732-3	•	•

For panel cutout dimensional data, see Section Q-Technical Reference

### Medium base Attachon with guard

Rating		Description	Catalog no.		
W	V/AC				
200	250	Phenolic socket (732), yellow guard, wire range #18 to #12 AWG, hook mounting	□ 1466Y	•	•

Compliances, specifications and availability are subject to change without notice.

 Indicates NAFTA compliant - Page Q-32

 RoHS compliant - Page Q-32