

Eaton 736W-BOX

Catalog Number: 736W-BOX

Eaton residential grade duplex receptacle, #14-12 AWG, 15A, Residential, Flush, 125V, Side wire, White, Brass, Thermoplastic, 1-15R, Duplex, Screw, Thermoplastic, ED Box



General specifications

Product Name	Catalog Number
Eaton residential grade duplex receptacle	736W-BOX
	UPC
	032664750663
Product Length/Depth	Product Height
1.31 in	4.19 in
Product Width	Product Weight
0.74 in	0.12 lb
Warranty	Certifications
Refer to warranty document.	cULus Listed
	Federal Specification Classification 6221 02

Product specifications

Device type

Receptacle

Color

White

Face/body material

Thermoplastic

Wiring method

Side wire

Features

Non-grounding

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Duplex receptacle

Device grade

Standard grade

NEMA configuration

1-15R

Style type

Standard

Design type

Straight blade

Connection type

Screw

Number of wires

Resources

Catalogs

[Residential Buyers Guide B-26](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 736W-BOX](#)

2

Receptacle type

Duplex

Voltage rating

125V

Application

Residential

Torque rating

14 lbf-inch

Packaging type

ED Box



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)