

Eaton 7501BK-BOX

Catalog Number: 7501BK-BOX

Eaton standard grade decorator switch, Box, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Black, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Single-pole, Thermoplastic 752407



General specifications

Product Name	Catalog Number
Eaton standard grade decorator switch	7501BK-BOX
UPC	Product Length/Depth
032664752407	1.44 in
Product Height	Product Width
4.19 in	0.97 in
Product Weight	Compliances
0.19 lb	RoHS Compliant NAFTA
Certifications	
cULus Listed	

Product specifications

Special features

Box

Switch type

Single-pole

Phase

Single-phase

Load type

INC

Fan

LED

CFL

HAL

Motor Control

ELV

MLV

FLR

Closure type

Maintained

Color

Black

Wiring method

Back and push

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Single-pole

Type

Switch decorator

Voltage rating

120/277 V

Resources

Brochures

[Decorator standard grade switches spec sheet](#)

Specifications and datasheets

[Eaton Specification Sheet - 7501BK-BOX](#)

Actuator
Decorator



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)