

Non-NEMA 3 Wire Plug, Yellow

7554SS



Turnlok Plug 3wire 15amp 125volt 10amp
250v



features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

specifications

General Info

Color: Yellow
Type: Plug

Number Of Wires: 3
Special Features: Non-NEMA

Listing Agencies/Third Party Information

UN SPS C: 39121403

Dimensions

Diameter U S: 1.531"
Length U S: 1.105"

Technical Information

Amps: 15 Amp
Volts: 125V
Volts A C: 125

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant