



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7555SS Turnlok Conn 3W 15A/125V 10A/250V

Pass & Seymour/Legrand

Catalog Number	7555SS
Manufacturer	Pass & Seymour/Legrand
Description	Turnlok Connector 3WIRE 15AMP 125VOLT 10AMP 250V
Weight per unit	0.1710 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15/10
Material	Nylon
Number of Wires	3
Poles	Consult the Factory
Voltage Rating	125/250
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	Consult the Factory

Material, Color, and Finish

Color	Yellow
-------	--------

Dimensions and Weight

Size	2.624 L x 1.531 H
------	-------------------

Descriptions

Description	TURNLOK CONN 3W 15A/125V 10A/250V
extra long description	P&S 7555SS DISC SUB 125VPSL515C,250
Long Description	Turnlok Connector 3wire 15amp 125volt 10amp 250v
Product Type	Disc Sub 125VPSL515C, 250V PSL615C
Special Features	Industrial-strength plug blades and connector contacts resist heat rise, provide excellent conductivity. Impact- and corrosion-resistant durable nylon shell material. Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire. Rounded back contour reduces snags and hang-ups on the job site. Visible stamped device rating.

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007755510
Manufacturers Part Number	7555SS
UPC	785007755510

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlok® Connector, Non-NEMA

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.171

Uses, Certifications, and Standards

Application	Industrial
environmental conditions	Consult the Factory
Mounting	Cord
nema rating	Non-NEMA
standard	Non-NEMA