

# Miscellaneous Accessories

## Lever Guards Blank Inserts Bushings



### Metal Switch Lever Guard

#### FEATURES

- Nickel finish.
- For flush tumbler switch levers.
- Attaches to standard plates by the plate screws.

#### Metal Switch Lever Guard

Description	Catalog No.
Switch lever guard with 0.25" (6.35mm) padlock holes	7949



7949

#### Sub-Frame and Blank Insert

Description	Color	Catalog No.
Blank insert and strap for any switch plate	Brown	756B
	Gray	756GY
	Ivory	756V
	Light Almond	756LA
	White	756W



756

### Bushings

#### FEATURES

- Provide smooth protective surface for cords or wires passing through knockouts.

#### Bushings

Description	Knockout Size	Inside Diameter	Outside Diameter	Groove	Catalog No.
Rubber	0.375" (9.525mm)	0.375" (9.525mm)	0.75" (19.05mm)	0.50" (12.70mm)	76
Rubber	0.50" (12.70mm)	0.50" (12.70mm)	1.031" (26.19mm)	0.875" (22.225mm)	77
Plastic with Lock Nut	0.50" (12.70mm)	0.50" (12.70mm)	—	—	28
Plastic with Lock Nut	0.75" (19.05mm)	0.75" (19.05mm)	—	—	30



76



28

## T-12 Cord Sets & Accessories

#### MATERIAL CHARACTERISTICS

Environmental:  
Bushings:  
Meets flammability requirements per UL 94, VO rated.  
Temperature Rating:  
76 and 77:  
-20°C to 70°C,  
28 and 30:  
-20°C to 60°C.