ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# 774011 Toggle Switch, SPST, On-Off, Screw

*Ideal*

| | |
|---|---|
| Catalog Number | 774011 |
| Manufacturer | Ideal |
| Description | Toggle Switch, 1 Pole, 10 A;20 A, 125/227 V Ac, SPST Contact Configuration, Solid Brass;Nickel-Plated (Bushing) Material, Screw Connection, Hole Mount, Nickel Plated (Bushing), 1.130 In (L) X 0.570 In (W) X 0.610 In (H), +32 °F Operating Temperature, +185 °F Operating Temperature, 0.11 LB |
| Weight per unit | 0.1126 (lbs/each) |
| Product Category | Gen Purpose Switches |

## Features

| | |
|---|---|
| action | SPST |
| amperage rating | 20,10 |
| connection | Screw, 2 Terminals |
| Contact Rating | Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating |
| operating cycles | 100000 |
| Poles | 1 |
| Switch Type | Toggle |

## Dimensions and Weight

| | |
|---|---|
| Height | 0.610 |
| Width | 0.570 |

## Descriptions

| | |
|---|---|
| Description | TOGGLE SWITCH, SPST, ON-OFF, SCREW |
| extra long description | IDEAL 774011 SWITCH,TOGGLE,SPST,O-F |
| Features | Great for power tool and motor control switch applicationsRugged long-wearing solid brass/nickel-plated bushings1/2 in. diameter mounting holeDielectric Strength: 1500VMechanical Life: 100,000 cyclesOperating Temperature: 32°F to 185°F (0°C to 85°C)DC?Rating: Factory tested 100,000 cycles to 21 Amp 14.8 VDC |

## Manufacturer Information

| | |
|---|---|
| Brand | Buchanan |
| GTIN | 00781789740119 |
| UPC | 781789740119 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | TOGGLE SWITCHES |
| Type | Standard, On-Off |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Availability

| | |
|---|---|
| Status | Inactive |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Weight Per each | 0.1126 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Mounting | 1/2 IN Hole Diameter |
| standard | CSA, RU Listed, RoHS |