ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
425 East Germann Road Suite 101
85297-0000, AZ Gilbert
Phone: 602-325-9757
Fax: 602-325-9758



774011 Toggle Switch, SPST, On-Off, Screw

Ideal

Catalog Number	774011
Manufacturer	Ideal
Description	Toggle Switch, 1 Pole, 10 A;20 A, 125/227 V Ac, SPST Contact Configuration, Solid Brass;Nickel-Plated (Bushing) Material, Screw Connection, Hole Mount, Nickel Plated (Bushing), 1.130 In (L) X 0.570 In (W) X 0.610 In (H), +32 °F Operating Temperature, +185 °F Operating Temperature, 0.11 LB
Weight per unit	0.1126 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	SPST
amperage rating	20,10
connection	Screw, 2 Terminals
Contact Rating	Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating
operating cycles	100000
Poles	1
Switch Type	Toggle

Dimensions and Weight

Height	0.610
Width	0.570

Descriptions

Description	TOGGLE SWITCH, SPST, ON-OFF, SCREW
extra long description	IDEAL 774011 SWITCH,TOGGLE,SPST,O-F
Features	Great for power tool and motor control switch applicationsRugged long-wearing solid brass/nickel-plated bushings1/2 in. diameter mounting holeDielectric Strength: 1500VMechanical Life: 100,000 cyclesOperating Temperature: 32°F to 185°F (0°C to 85°C)DC?Rating: Factory tested 100,000 cycles to 21 Amp 14.8 VDC

Manufacturer Information

Brand	Buchanan
GTIN	00781789740119
UPC	781789740119

Taxonomies, Classifications, and Categories

Category Description	TOGGLE SWITCHES
Type	Standard, On-Off

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
425 East Germann Road Suite 101
85297-0000, AZ Gilbert
Phone: 602-325-9757
Fax: 602-325-9758

Availability

Status	Inactive

Packaging

Carton	1
Weight Per each	0.1126

Uses, Certifications, and Standards

Mounting	1/2 IN Hole Diameter
standard	CSA, RU Listed, RoHS