



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 774093 Toggle Switch, SPST, (O)-F, Screw, 15a

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 774093  |
| Manufacturer     | Ideal   |
| Description      | Ideal, Toggle Switch, Standard, (On)-Off, Voltage Rating: 125, 227 Vac, Amperage Rating: 20, 10 Amp, Number Of Poles: 1, Action: SPST, Connection: Screw, 2 Terminals, Actuator: Toggle, Contact Rating: Factory Tested 100000 Cycles to 21 Amp 14.8 VDC DC Rating, Size: 1.130 In Length X 0.570 In Width X 0.610 In Height, Mounting: 1/2 In Hole Diameter, Operating Cycles: 100000 Cycles Mechanical Life, Operating Temperature: 32 to 185 Deg F, Dielectric Strength: 1500 V, Finish: Solid Brass/Nickel-Plated Bushings, |
| Weight per unit  | 0.1500 (lbs/each)   |
| Product Category | Gen Purpose Switches  |

### Features

|                  |   |
|------------------|---|
| action           | SPST  |
| actuator         | Toggle  |
| amperage rating  | 10/20   |
| connection       | Screw, 2 Terminals  |
| Contact Rating   | Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating |
| operating cycles | 100k  |
| Poles            | 1   |
| Voltage Rating   | 125/227   |

### Dimensions and Weight

|      |  |
|------|--|
| Size | 1.130 IN Length X 0.570 IN Width X 0.610 IN Height |
|------|--|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                  |   |
|------------------|---|
| Description      | TOGGLE SWITCH, SPST, (O)-F, SCREW, 15A  |
| Features         | Great for power tool and motor control switch applications Rugged long-wearing solid brass/nickel-plated bushings 1/2 in. diameter mounting hole Dielectric Strength: 1500V Mechanical Life: 100,000 cycles Operating Temperature: 32°F to 185°F (0°C to 85°C) DC Rating: Factory tested 100,000 cycles to 21 Amp 14.8 VDC  |
| Long Description | IDEAL, Toggle Switch, Standard, (On)-Off, Voltage Rating: 125, 227 VAC, Amperage Rating: 20, 10 AMP, Number Of Poles: 1, Action: SPST, Connection: Screw, 2 Terminals, Actuator: Toggle, Contact Rating: Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating, Size: 1.130 IN Length X 0.570 IN Width X 0.610 IN Height, Mounting: 1/2 IN Hole Diameter, Operating Cycles: 100000 Cycles Mechanical Life, Operating Temperature: 32 To 185 DEG F, Dielectric Strength: 1500 V, Finish: Solid Brass/Nickel-Plated Bushings, |
| Product Type     | Switch, TGL, SPST, (O)-F, SCRW  |
| Special Features | Features: Great For Power Tool And Motor Control Switch Applications; Rugged Long-Wearing Solid Brass/Nickel-Plated Bushings; 1/2 IN Diameter Mounting Hole; Dielectric Strength: 1500 V; Mechanical Life: 100000 Cycles; Operating Temperature: 32 DEG F To 185 DEG F (0 DEG C To 85 DEG C); DC Rating: Factory Tested 100000 Cycles To 21 AMP 14.8 VDC; Bulk Packaging Of 100 Available Upon Request; Dielectric Strength: 1500 V; Finish: Solid Brass/Nickel-Plated Bushings; Hp Rating: 3/4 HP At 125 To 250 VAC            |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250603732 |
| Manufacturers Part Number | 774093         |
| UPC                       | 783250603732   |

## Taxonomies, Classifications, and Categories

|                      |                          |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type                 | Standard, (On)-Off       |

## Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.15 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                       |  |
|-----------------------|--|
| Application           | For Power Tool And Motor Control Switch Applications |
| Mounting              | 1/2 IN Hole Diameter                                 |
| Operating Temperature | 32 To 185  |
| standard              | CSA, RU Listed, RoHS                                 |