



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7802MD 30A 2P SNGL PH Ac Motor Disconnect

*Pass & Seymour/Legrand*

Catalog Number	7802MD
Manufacturer	Pass & Seymour/Legrand
Description	Motor Disconnecter, 2 Poles, 30 A, 600 V Ac, 1.753 (L) X 1.825 (W) X 2.375 (H) In, Box Mount, -40 °C Operating Temperature, +75 °C Operating Temperature, Toggle Actuator, 0.31 LB
Weight per unit	0.3100 (lbs/each)
Product Category	Misc Wiring Devices

### Features

actuator	Toggle
amperage rating	30
connection	Side & Back Wired
indoor/outdoor	Indoor
load	30A
Load Rating	30 A @ 600 VAC
Load Type	LED, Xenon, Fluorescent, Universal, Halogen, Incandescent, CFL
Material	Thermoplastic
Number of Gangs	1
Number of Switches	1.0
operating cycles	50000
Poles	2
supply voltage	120.0
Switch Type	Toggle
throw type	Double Throw
Voltage	600.0 V
Wall Plate Included	NO
Wattage	600
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	1.753" Depth x 1.825" Width x 2.375" Height
------	---

### Descriptions

Description	30A 2P SNGL PH AC MOTOR DISCONNECT
extra long description	P&S 7802MD 30A 2P SNGL PH AC MOTOR



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007267655
Manufacturers Part Number	7802MD
UPC	785007267655

## Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	Tamper-Resistant, Manual Controller

## Trade Size

Amperage	30.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.31

## Uses, Certifications, and Standards

environmental conditions	UL94 V2
Frequency Rating	60Hz
Mounting	BOX
Operating Temperature	Maximum continuos +75°C, minimum -40°C
standard	CULUS, CSA Listed, UL Listed