



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7813PMD 30A 3P 3 PH Ac MD, Nema 1 Enc *Pass & Seymour/Legrand*

Catalog Number	7813PMD
Manufacturer	Pass & Seymour/Legrand
Description	Ac Manual Motor Controller, Suitable As Motor Disconnect - 10KA @ 600VAC, 30A Max. Class J Fuse.
Weight per unit	0.7180 (lbs/each)
Product Category	Misc Wiring Devices

### Features

actuator	Toggle
amperage rating	30
connection	Side & Back Wired
Enclosure Type	Nema 1
load	30A
operating cycles	50000
Poles	3
Voltage	600.0 V
Voltage Rating	600

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Size	2.8" Depth x 2.825" Width x 3.91" Height
------	--

### Descriptions

Description	30A 3P 3 PH AC MD, NEMA 1 ENC
extra long description	P&S 7813PMD 30A 3P 3 PH AC MD, NEMA
Long Description	AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.
Product Type	30A 3P 3 PH Ac MD, Nema 1 Enc
Special Features	Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007267693
Manufacturers Part Number	7813PMD
UPC	785007267693

### Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	Manual Controller



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 30.0

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.718

## Uses, Certifications, and Standards

Application ..... Commercial/Industrial

Enclosure ..... NEMA 1

environmental conditions ..... UL94 V2

Frequency Rating ..... 60Hz

Mounting ..... FLUSH

Operating Temperature ..... Maximum continuous +75°C, minimum -40°C

standard ..... CULUS, CSA Listed, UL Listed