



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7813PMD 30A 3P 3 PH Ac MD Nema 1 Enc *Pass & Seymour/Legrand*

| | |
|------------------|--|
| Catalog Number | 7813PMD |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Ac Manual Motor Controller, Suitable As Motor Disconnect - 10KA @ 600VAC, 30A Max. Class J Fuse. |
| Weight per unit | 0.7180 (lbs/each) |
| Product Category | Misc Wiring Devices |

Features

| | |
|------------------|-------------------|
| actuator | Toggle |
| amperage rating | 30 |
| connection | Side & Back Wired |
| Enclosure Type | Nema 1 |
| load | 30A |
| operating cycles | 50000 |
| Poles | 3 |
| Voltage | 600.0 V |
| Voltage Rating | 600 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|--|
| Size | 2.8" Depth x 2.825" Width x 3.91" Height |
|------|--|

Descriptions

| | |
|------------------------|--|
| Description | 30A 3P 3 PH AC MD NEMA 1 ENC |
| extra long description | P&S 7813PMD 30A 3P 3 PH AC MD, NEMA |
| Long Description | AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse. |
| Product Type | 30A 3P 3 PH Ac MD, Nema 1 Enc |
| Special Features | Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007267693 |
| Manufacturers Part Number | 7813-PMD |
| UPC | 785007267693 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Industrial switches |
| Type | Manual Controller |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 30.0

Packaging

Carton 1

Package 10

Weight Per each 0.718

Uses, Certifications, and Standards

Application Commercial/Industrial

Enclosure NEMA 1

environmental conditions UL94 V2

Frequency Rating 60Hz

Mounting FLUSH

Operating Temperature Maximum continuous +75°C, minimum -40°C

standard CULUS, CSA Listed, UL Listed