



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7842MD 40A 2P SNGL PH Ac Motor Disconnet

Pass & Seymour/LeGrand

Catalog Number	7842MD
Manufacturer	Pass & Seymour/LeGrand
Description	Double-Pole, Single Phase Switch (7842), 40 Amps, 600VS
Weight per unit	0.3100 (lbs/each)
Product Category	Misc Wiring Devices

Features

actuator	Toggle
amperage rating	40
connection	Side & Back Wired
load	40A
operating cycles	50000
Poles	2
Voltage	600.0 V
Voltage Rating	600
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Black
Finish	Matte

Dimensions and Weight

Size	1.753" Depth x 1.8255" Width x 2.375" Height
------	--

Descriptions

Description	40A 2P SNGL PH AC MOTOR DISCONNENET
extra long description	P&S 7842MD 40A 2P SNGL PH AC MOTOR
Long Description	Double-Pole, Single Phase Switch (7842), 40 Amps, 600Vs
Product Type	40A 2P SNGL PH Ac Motor Disconnet
Special Features	Double Pole, Single Phase Switch, Canada Only Motor Disconnect

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007267716
Manufacturers Part Number	7842-MD
UPC	785007267716

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	Manual Controller

Trade Size

Amperage	40.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.31

Uses, Certifications, and Standards

Application	Commercial/Industrial
environmental conditions	UL94 V2
Frequency Rating	60Hz
Mounting	BOX
Operating Temperature	Maximum continuos +75°C, minimum -40°C
standard	CULUS, CSA Listed, UL Listed