

Fluorescent Lampholders Shallow Base



T8 & T12 Slimline Single Pin Fluorescent Sockets



80-1496 Plunger
1 3/4" H x 1 1/4" W x 1 1/4" Dia.



80-1497 Fixed
1 3/4" H x 1 1/4" W x 1 1/4" Dia.

Shallow Base
Slide-On Quickwire for
Wet and Damp Locations
Rapid Start for 20 Gauge Panels
Strip 3/8" - 1/2"
660W-1000V

High Output 800 MA -1500 MA — Recessed Double Contact



80-2129 Plunger
2 1/4" H x 1 1/4" W x 1 1/2" Dia.



80-2130 Fixed
2 1/4" H x 1 1/4" W x 1 1/2" Dia.

Shallow Base
for Slide On Quickwire
Power Groove and
Jacketed Lamps
20 Gauge Panels
Strip 3/8" - 1/2"
660W-600V

T8 & T12 (HO) High Output Fluorescent Sockets - Recessed Double Contact



80-1498 Plunger
1 7/8" H x 1 3/8" W x 1 1/4" Dia.



80-1499 Fixed
1 7/8" H x 1 3/8" W x 1 1/4" Dia.

Quickwire Terminals
Accept Up To 18 Gauge
Solid or Tinned Leads
Slide-On Shallow Base
Rapid Start
Strip 3/8" - 1/2"
660W-1000V