

# Eaton 805V-BOX

Catalog Number: 805V-BOX

Eaton Arrow Hart heavy-duty flush mount receptacle , #4 AWG, 20A, Industrial, Flush, 125/250V, Side wire, Ivory, Brass, Nylon, 10-20R, Single, Screw, Nylon, ED Box



## General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty flush mount 805V-BOX receptacle	UPC 032664181603
Product Length/Depth 1.81 in	Product Height 3.28 in
Product Width 1.42 in	Product Weight 0.228 lb
Warranty Refer to warranty document.	Certifications UL NOM Federal Specification Classification 6233 01

## Product specifications

### Device type

Receptacle

### Color

Ivory

### Face/body material

Nylon

### Wiring method

Side wire

### Material

Nylon

### Mounting method

Flush

### Allowable wire size

#4 AWG

### Amperage Rating

20A

### Number Of Poles

Three-pole

### Contact material

Brass

### Type

Single receptacle

### Device grade

Heavy-duty industrial specification grade

### NEMA configuration

10-20R

### Style type

Standard

### Design type

Straight blade

### Connection type

Screw

### Number of wires

3

### Receptacle type

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Specifications and datasheets

[Eaton Specification Sheet - 805V-BOX](#)

Single

Voltage rating

125/250 V

Application

Industrial

Torque rating

14 lbf-inch

Packaging type

ED Box



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)