




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



80PVC212 SCH 80 2-1/2" 10' PVC Conduit

Heritage Plastics

| | |
|------------------|--|
| Catalog Number | 80PVC212 |
| Manufacturer | Heritage Plastics |
| Description | PVC Conduit, Underground or Aboveground Application, Gray Color, 2.250 In Conduit Inner Diameter, 2.875 In Conduit Outer Diameter, 10 FT Length, Made In Usa, +90 °C Maximum Operating Temperature, 930 FT/PK Package Quantity, Belled End;Corrosion Resistant;Rust Resistant;Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 80 Special Features, Intertex Etl Listed Us;UI 651 and Nema TC2 Standards Met, 2-1/2 In Trade Size, 0.276 In Wall Thickness, 1.463 LB Weight |
| Weight per unit | 1.5 (lbs/each) |
| Product Category | PVC SCH 80 Conduit |

Descriptions

| | |
|-------------|-------------------------------|
| Description | SCH 80 2-1/2" 10' PVC CONDUIT |
|-------------|-------------------------------|

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | PVC Schedule 80 Conduit |
|----------------------|-------------------------|

Availability

| | |
|-------------|----|
| minimum qty | 10 |
|-------------|----|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 930 |
| Weight Per foot | 1.463 |