



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



810DCI2 2" 90D Diecast Ins Conn

Bridgeport Fittings

| | |
|------------------|---|
| Catalog Number | 810DCI2 |
| Manufacturer | Bridgeport Fittings |
| Description | Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 2 Inch |
| Weight per unit | 1.4 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|----------------|---------------|
| angle | 90 DEG |
| Connector Type | FMC |
| Material | Zinc Die Cast |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Dimensions and Weight

| | |
|------|---|
| Size | 2 |
|------|---|

Descriptions

| | |
|------------------------|---|
| Description | 2" 90D DIECAST INS CONN |
| extra long description | BPT 810-DCI2 2" 90 DEG CONN. INS. Z |
| Long Description | Connector, 90 Degrees, Zinc Die Cast, Insulated Throat, Flex Size 2 Inch |
| Product Type | 2" 90 Deg Conn. Ins. Zinc |
| Special Features | Furnished with 2-way Phillips/Slotted Head Screw |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747168108 |
| Manufacturers Part Number | 810-DCI2 |
| UPC | 781747168108 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | FLEX & MC FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|---|
| Trade Size | 2 |
|------------|---|

Packaging

| | |
|-----------------|------|
| Carton | 5 |
| Weight Per each | 1.42 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Application | 90 Degrees connector suitable for use to connect flexible metal conduit to box or enclosure. Insulator rated 105 degrees C. |
| standard | UL, CSA |
| Temperature Rating | 105°C |