



COMBINATION BOX/CONDUIT HANGER FOR 1/2-3/4" EMT

CATALOG NUMBER

812MB18A



The nVent CADDY B18 Combination Box/Conduit Hanger presents an efficient and secure solution for the installation of electrical boxes and conduit in overhead applications by streamlining the process with a single-threaded rod drop. The system is designed to provide greater efficiency in the field with our class-leading range of nVent CADDY Conduit Clamps.

CERTIFICATIONS



FEATURES

Scoreline breakaway feature can be easily modified by hand while maintaining UL listing

Eliminates need for offset bending conduit

Designed to be versatile and reusable

Labor and time savings due to built-in first means of support

NEC® & CEC compliant

PRODUCT ATTRIBUTES

Material: Steel;Spring Steel

Finish: Pregalvanized;nVent CADDY Armour

EMT Conduit Size: 1/2";3/4"

Hole Size (HS): 1/4"

Hole Type: Plain

Screw Included: No


Length (L): 18"

Width (W): 2.1"

ADDITIONAL PRODUCT DETAILS

NEC® 300.11 requires dedicated drop wire/rod. For single and multiple runs of conduit.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER