

# Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 15A, 125V, Ivory

8200HI



Heavy-Duty Hospital Grade Compact  
Design Duplex Receptacle Back & Side  
Wire 15amp 125volt Ivory



## features & benefits

- Impact-resistant nylon face.
- One-piece heat-treated triple-wipe brass power contacts.
- Easily accessible break-off line contact connecting tab for split circuit wiring.
- Corrosion-resistant, zinc-plated steel strap is locked in.
- Internal screw-pressure-plate back wire and side wire line terminals accept #14 – #10 AWG copper or copper-clad conductors.
- High strength thermoplastic back body.
- Back wire holes allow entry of conductor insulation partially into body but not into wiring compartment.
- Auto-ground clip assures positive ground.
- Compact design for easy installation.
- Tri-drive terminal and mounting screws.

## specifications

### General Info

Color: Ivory  
Type: Compact Design, Receptacles  
Duty: Heavy Duty  
Special Features: Back, Side Wire

### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406  
UR: No

**Dimensions**

Depth U S: .780"  
Height U S: 3.281"  
Width U S: 1.322"

**Technical Information**

Amps: 15 Amp  
Volts: 125V  
Volts A C: 125  
Capacity: Duplex  
Grade Type: Hospital

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant