



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 8300RED Hosp GRD Duplex Recept 20A/125VAC RD

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | 8300RED   |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V |
| Weight per unit  | 0.2500 (lbs/each)   |
| Product Category | Gen Purpose Recept & Surge Pro  |

### Features

|                     |  |
|---------------------|--|
| amperage rating     | 20   |
| connection          | Back and side wire                               |
| Dielectric Strength | Withstands 2000V minimum                         |
| indoor/outdoor      | Indoor   |
| Material            | Nylon  |
| Number of Wires     | 3  |
| Outlet Type         | Indoor, Commercial                               |
| Poles               | Double Pole                                      |
| Voltage             | 125.0 V  |
| Voltage Rating      | 125  |
| Wattage             | Electrical power is expressed in Amps and Volts. |
| Wire Size           | 14 - 10  |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | Red   |
| Finish | Matte |

### Dimensions and Weight

|        |       |
|--------|-------|
| Height | 3.281 |
| Width  | .900  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | HOSP GRD DUPLEX RECPT 20A/125VAC RD  |
| extra long description | P&S 8300RED HOSP GRD DUP RECEPT 20A  |
| Long Description       | Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V  |
| Product Type           | Hosp GRD Dup Recept 20A/125VAC Red   |
| Special Features       | One-piece nickel-plated brass mounting strap with integral ground. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Two drive screws anchor strap to back body and face. Exclusive patented feature, circuit label on face allows permanent circuit identification. .040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant |

## Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007830101   |
| Manufacturers Part Number | 8300-RED         |
| UPC                       | 785007830101     |

## Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type                 | Outlet                 |

## Trade Size

|          |      |
|----------|------|
| Amperage | 20.0 |
|----------|------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 100  |
| Weight Per each | 0.25 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Commercial                                    |
| environmental conditions | Flammability: UL94 V2 and UL94-5 VA           |
| Mounting                 | WALL  |
| nema rating              | 5-20R   |
| standard                 | CULUS, FEDSPEC, cULus UL498, CSA C22.2 No. 42 |
| Temperature Rating       | -40° - 60° C                                  |