



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8300WMRI Hosp GRD Duplex Recp 20A 125V Mri WH

Pass & Seymour/Legrand

Catalog Number	8300WMRI
Manufacturer	Pass & Seymour/Legrand
Description	Extra Heavy-Duty Hospital Grade Mri Duplex Receptacle Back and Side-Wire 20A 125V
Weight per unit	0.1667 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
Material	Nylon
Number of Wires	3
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Dimensions and Weight

Height	3.281
Width	.900

Descriptions

Description	HOSP GRD DUPLEX RECP 20A 125V MRI WH
extra long description	P&S 8300WMRI HOSP GRD DUP RECP 20A
Long Description	Extra Heavy-Duty Hospital Grade MRI Duplex Receptacle Back and Side-Wire 20A 125V
Product Type	Hosp GRD Dup Recp 20A 125V Mri W
Special Features	Designed expressly for MRI applications. Exclusive patented feature, circuit label on face allows permanent circuit identification. Extra heavy-duty one-piece nickel-plated brass mounting strap with integral ground for superior structural integrity and long-term performance. .036 inch thick, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Easily accessed break-off, line-contact connecting tab for



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007269178
Manufacturers Part Number	8300-WMRI
UPC	785007269178

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Hospital Grade MRI Receptacle, Extra Heavy-Duty

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.1667

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CULUS, UL498, CSA C22.2 No. 42, FEDSPEC