
84562

F96T12 CW/HO-O/ALTO/R (PK X 15)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Average Life Hours: 14000

Base: Recessed Double Contact (R17d)

Bulb: T12

Coating: Copolymer

Color: Cool White

Color Temperature: 4100K

CRI: 62

Diameter: 1.50 IN

Initial Lumens: 8800

Lamp Type: Fluorescent

Length: 96.00 IN

Mean Design Lumens: 7650

Package (LxWxH): 96.25 IN x 8.75 IN x 5.25 IN

Package Weight: 22.70 L

Pack By: 15

Shape: T

Special Features: Shatter-Resistant

Type: Straight Linear Fluorescent Lamp

UPC: 726585845620

Wattage: 110.0 W

ULEPH,ROHS,NSF Non-Food Zone,NSF Splash Zone

84562

F96T12 CW/HO-O/ALTO/R (PK X 15)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Average Life Hours: 14000

Base: Recessed Double Contact (R17d)

Bulb: T12

Coating: Copolymer

Color: Cool White

Color Temperature: 4100K

CRI: 62

Diameter: 1.50 IN

Initial Lumens: 8800

Lamp Type: Fluorescent

Length: 96.00 IN

Mean Design Lumens: 7650

Package (LxWxH): 96.25 IN x 8.75 IN x 5.25 IN

Package Weight: 22.70 L

Pack By: 15

Shape: T

Special Features: Shatter-Resistant

Type: Straight Linear Fluorescent Lamp

UPC: 726585845620

Wattage: 110.0 W

ULEPH,ROHS,NSF Non-Food Zone,NSF Splash Zone