



8510	4"	8.700	1.031	10.200	3.675	4.425
859	3 1/2"	7.500	1.031	9.400	3.275	3.950
858	3"	6.700	1.031	7.875	2.950	3.450
857	2 1/2"	6.125	.875	7.187	2.450	2.975
PART No.	TRADE SIZE	"A"	"B"	"C"	MIN	MAX